

K1550 range of Katharometers

Thermal conductivity analysers for binary gas mixtures

- Measured gases include: H₂, He, Ar, CO₂, Kr, Ne and Xe
- Proven technology from the katharometer experts
- Hazardous area options
- Corrosive gas sensor options
- Non-depleting remote sensor
- Fixed and variable compensation

APPLICATIONS

- Hydrogen analysis
- Syngas
- Gasification
- Helium recovery
- Gas mixing
- Nitriding furnaces
- Fuel cell research



The **K1550 range of analysers** are ideal for measuring the % level of one gas in a binary or pseudo-binary mixture. For example, air is composed of many gases but in known, fixed ratios, therefore hydrogen in air is a pseudo-binary mixture and can be measured with the K1550.

Hydrogen, helium, dissociated ammonia and noble gases such as krypton and xenon are all well suited to this technique. In particular, katharometers are well suited to gases that have no dedicated sensor and therefore provide cost effective analysis solutions.

A compensation input is available as an option, either fixed or variable, via a 4-20 mA input. This extends the capability of the analyser to measure in more complex mixtures. The KG1550 series also features an integral oxygen sensor.

All versions are available with a 0 – 100% range. 0 – 20% and 80 – 100% ranges are also available, depending on the measured gas and the background. Hydrogen analysers can also be supplied with a 0 – 5% range. Multi-range instruments are sometimes available on request.

Different sample conditioning systems are available, standard or

bespoke, according to the process conditions. For corrosive gases a variety of sensor assemblies and fittings are available to suit the specific gas. Eaton are prepared to recommend complete systems on receipt of full gas stream specifications.

For hazardous area applications the sensor may be mounted remotely in the hazardous area and connected through an MTL zener barrier to the electronics unit in a safe area. Alternatively, the electronics unit can be supplied in an Ex d enclosure, with a remote keypad for non-intrusive calibration, for full hazardous area use.

K1550 range of Katharometers

March 2021

SPECIFICATION

Ranges available

(Depends upon measured/background gas)
 0 - 20%, 80 - 100%, 0 - 100% for most gases
 0 - 5%, for most hydrogen ranges
 Consult Eaton for gas type and range

Stability

<1 % f.s.d./month

Accuracy

±2% f.s.d. depending upon span and gas

Repeatability

<1% f.s.d.

Speed of response

T90: 20 seconds (typ.)

Sample flow

100-300ml/min for optimum performance

Sample pressure

Nominally atmospheric, set by vent pressure

Sample connections

Inlet and outlet: Captive seal compression suitable for 0.25inch (or 6mm) outside diameter tube

Display

LCD 2 or 4 lines of alphanumeric characters

Analogue output

4-20mA
 (User-programmable)

Outputs (alarm)

Two alarms: each user-configurable to OFF, HIGH or LOW

Relay outputs

Rated at 30V ac or dc, 0.5A, normally energised

Ambient operating temperature range

Sensor: -10°C to 40°C
 Electronics: 0°C to 40°C
 (0-90% R.H. non-condensing)

Storage temperature range

-5°C to +55°C
 (0-90% R.H. non-condensing)

Supply Voltage

110/120V or 220/240V AC, 50/60Hz

Power consumption

12VA

MOUNTING

Electronics unit

Panel mounting with two clamps

Remote sensor unit

Wall/ bulkhead

MATERIALS

Enclosure

Glassfibre-reinforced Noryl to IP40 (IP54 locking door option)

Remote sensor

Supplied in a remote housing with flowmeter and needle valve

K1550FX (HAZARDOUS AREA VERSION)

As above specification but with certified stainless steel sensor block and MTL zener barrier (supplied loose)



Option

Ex d enclosure for K1550FX electronics unit

ORDERING INFORMATION

Specify	Measured gas	Background gas	Range	Output	Supply voltage	Options
K1550R	Specify	Specify	0 - 100% 0 - 20%, 80 - 100%	4-20mA	110V or 220V	Compensation input
K1550FX	Specify	Specify				Ex d enclosure

DIMENSIONS



K1550FX electronics unit in optional Ex d enclosure with remote keypad

APPROVALS (ATEX Directive - Europe) for K1550FX version

Authority	Product/Cert. No.	Standards	Approved for
DEMKO	210 Gas detection head DEMKO02ATEX132848X	EN50014 EN50018	⊕ II 2G Ex d IIB + H ₂ T6 -40°C ≤ T _a ≤ 40°C ⊕ II 2G Ex d IIB + H ₂ T3 -40°C ≤ T _a ≤ 150°C
SGS/ BASEEFA	MTL7766Pac BAS01ATEX7217 IECExBAS04.0025	IEC60079-0 IEC60079-11	⊕ II 1GD [Ex ia] IIC T6 -20°C ≤ T _a ≤ 60°C
ISSeP	Ex d enclosure Pending		⊕ II 2GD Ex d IIC T6 (85°C) or T5 (100°C)



Powering Business Worldwide

Eaton Electric Limited,
 Great Marlings, Butterfield, Luton
 Beds, LU2 8DL, UK.
 Tel: + 44 (0)1582 723633 Fax: + 44 (0)1582 400901
 E-mail: mtlgas@eaton.com
 www.mtl-inst.com

© 2021 Eaton
 All Rights Reserved
 Publication No. EPS 500-0010 Rev 8 010321
 March 2021

EUROPE (EMEA):
 +44 (0)1582 723633
 mtlenquiry@eaton.com

THE AMERICAS:
 +1 800 835 7075
 mtl-us-info@eaton.com

ASIA-PACIFIC:
 +65 6 645 9888
 sales.mtlsing@eaton.com

The given data is only intended as a product description and should not be regarded as a legal warranty of properties or guarantee. In the interest of further technical developments, we reserve the right to make design changes.