September 2016 EPS F11-Labkit rev 2

CROUSE-HINDS SERIES

F11 Labkit

Power conditioner and cables for temporary fieldbus network

- Built-in fieldbus power conditioning
- 5 fieldbus device ports
- 30mA current per device
- Up to 315mA total current
- Auxiliary port for expansion
- Fieldbus device cable and interface card cable
- Complete with AC power supply
- Battery-pack option

The Relcom Fieldbus Labkit (F11-Labkit) is a convenient kit containing the Relcom Fieldbus Power Hub (F11) and a pair of cables (FCS-A05). Ideal for benchtops, labs, demonstrations and test setups, the Power Hub is a mini fieldbus segment in a box - just add devices and a host. The supplied cables allow connection to a fieldbus device and a National Instruments Fieldbus Interface card (USB, PCMCIA, or PCI).

A plug-in wall transformer with an input voltage range of 100-240VAC (50-60Hz) is included with the Power Hub. Adapters are supplied with the transformer for four different country power outlets (North America, Europe, UK, and Australia).

Internally the Power Hub contains a fieldbus power conditioner, two built-in terminators, and SpurGuard[™] current limiters. There are five ports for attaching devices (gray connectors), and an Auxiliary Port (black connector) for connection of additional devices. Pluggable screw terminal connectors are used on all ports for the fieldbus connections. The connectors may be secured to the Power Hub with the two retaining screws if desired.

A minimum of 30mA is available for each device port. If the current requirements of a Fieldbus device exceed the capability of the Device port, the Auxiliary Port can be used to provide additional power conditioned current. A total of 315mA can be supplied by the Power Hub. If any of the Device Ports or the Auxiliary Port is overloaded, a red Overload indicator will light.



For applications where AC power may not be available, the FCS-A11 Battery Pack may be used to supply power to the Power Hub. For more information on the FCS-A11 Battery Pack, see our datasheet EPS FCS-A11.

For convenience, the Power Hub can be mounted on standard 'top hat' 35mm DIN rail.

A typical use for the Power Hub is to configure, precommission, test, or calibrate fieldbus devices. In this case, the fieldbus device and host device (Emerson 375 or 475, National Instruments Fieldbus Interface, etc.) are connected to the Power Hub. No other components are required to have a functioning fieldbus segment.

Note: The F11 Power Hub is not intended to be used in a permanent installation.



Eaton Electric Limited, Great Marlings, Butterfield, Luton Beds, LU2 8DL, UK. Tel: + 44 (0)1582 723633 Fax: + 44 (0)1582 422283 E-mail: mtlenquiry@eaton.com www.mtl-inst.com

© 2016 Eaton All Rights Reserved Publication No. EPS F11-Labkit rev 2 September 2016

SPECIFICATIONS

ELECTRICAL

Device Port Rated Current

30mA **Total Current for all Device Ports and Auxiliary Port** 315mA max. (for specified operation) **Device Port Short Circuit Protection** Continuous protection against damage Maximum Fieldbus Cable Length 120 metres **Auxiliary Port Short Circuit Protection** Continuous protection against damage Wall-mounted Bulk Power Supply Input voltage: 100 - 240V AC, 50/60Hz Output voltage: 24V DC (nominal) **Fieldbus Device Cable** 1m - shielded twisted pair **National Instruments Cable** 1m - DB9 to prepared wires MECHANICAL

Fieldbus Connectors

Six sets, pluggable screw-terminal, with two securing screws

Mounting requirements

35mm DIN rail

Wire capacity

0.14 to 2.5mm²

Case material

Lexan polycarbonate

Temperature range

0° to +50°C


Weight


146g (nominal)


PHYSICAL NETWORK

IEC 61158-2


CASE DIMENSIONS







Connection diagram



ORDERING INFORMATION F11 Relcom Fieldbus Labkit

Foundation[™] fieldbus H1

Profibus PA

Battery Pack (Power Hub power in the field)	FCS-A11
Heavy-duty DIN rail end stop	FCS-A06
35mm DIN rail, aluminium, 1 meter	FCS-A01

Wall Power Supply and

Interchangeable Power Outlet Adapters (included with F11)



Powering Business Worldwide

Eaton Electric Limited, Great Marlings, Butterfield, Luton Beds, LU2 8DL, UK. Tel: + 44 (0)1582 723633 Fax: + 44 (0)1582 422283 E-mail: mtlenquiry@eaton.com www.mtl-inst.com

F11-Labkit

© 2016 Eaton All Rights Reserved Publication No. EPS F11-Labkit rev 2 260916 September 2016

F11 together with optional FCS-A11 Battery Pack



EUROPE (EMEA): +44 (0)1582 723633 mtlenguiry@eaton.com

THE AMERICAS: +1 800 835 7075 mtl-us-info@eaton.com

ASIA-PACIFIC: +65 6 645 9888 sales.mtlsing@eaton.com The given data is only intended as a product description and should not be regarded as a legal warranty of properties or guarantee. In the interest of further technical developments, we reserve the right to make design changes.